

# Connector, Parallel Groove

by ANDERSON  
Catalog ID: KR6

Two bolt Bronze Parallel Groove Connector

- Has no cable separator.



\* Representative image

## Product Details

### General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318828

### Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Weight	1.274 lb

### Conductor Related

Conductor Diameter (Tap) - Maximum	1.031 in
Conductor Diameter (Tap) - Minimum	0.292 in

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.675 in
Conductor Diameter Range	0.675 - 1.031

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	800 EA
-----------------	--------

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)