



* Representative image

Grounding Clamp

by ANDERSON
Catalog ID: KS10

Grounding Clamp, Copper Split-Bolt, Threaded Stud, One Cable

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Bronze
Number of Stud Threads	13
UPC	096359318880

Dimensions

Diameter - Stud	0.5 in
Weight	0.196 lb

Conductor Related

Conductor Diameter (Ground Tap) - Maximum	0 in
Conductor Diameter (Ground Tap) - Minimum	0 in
Conductor Diameter - Maximum	0.368 in
Conductor Diameter - Minimum	0.258 in
Conductor Diameter Range	0.258 - 0.368
Conductor Type	Copper
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com