

NOC-1.5R

NONI 1.5" ROUND CYLINDER FAMILY

ORDERING GUIDE

Examples: NOC-1.5RDL-CHNCSMCL-HO25927K-DM1NUGTCLR/NOC-1.5RDL-TRM-RPP

CATALOG #

HOUSING

NOC-1.5R		CHN			Optic Type	
Series/Category/Size/Shape	Function	Housing	Canopy	Mounting		
NOC-1.5R Noni Cylinder Family 1.5" Round	DL Downlight	CHN Cylinder Housing	CS Canopy - Standard CC Canopy - Conduit	CMBL Cable/Cord 6ft Black Cord ² CMWH Cable/Cord 6ft White Cord ² CM15BL Cable/Cord 15ft Black Cord CM15WH Cable/Cord 15ft White Cord PR Stem - Rigid (Standard) Nominal 18" length from cylinder top to ceiling ¹ PR_ Stem - Rigid (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" ¹ P Stem - Swivel (Standard) Nominal 18" length from cylinder top to ceiling ¹ P_ Stem - Swivel (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" ¹ SU Surface	High-CBCP Optic	
	LW Lensed Wall Wash				HO25 25° HO30 30° HO35 35° HO40 40° HO45 45° Wall Wash Optic LWLW Lensed Wall Wash ⁴	

CRI/CCT	DM1	Control Options	U	Cylinder Housing Color	Lens ³
927K 90 CRI, 2700K 930K 90 CRI, 3000K 935K 90 CRI, 3500K 940K 90 CRI, 4000K 830K 80 CRI, 3000K 835K 80 CRI, 3500K	DM1 0-10V, ELV, TRIAC 1%	N None	U Universal Voltage 120-277V	Texture WH White GY Gray BL Black GT Graphite PP Pink Panache GH Grasshopper Smooth WHS White GYS Gray BLS Black COS Copper AMW Anti-Microbial White Other X Custom Finish	CLR Clear FRS Frosted HEX Hex Cell Louver LIN Linear Spread NON No Lens SOL Solite

TRIM

NOC-1.5R		TRM	
Series/Category/Size/Shape	Function	Housing	Reflector Insert Color
NOC-1.5R Noni Cylinder Family 1.5" Round	DL Downlight LW Lensed Wall Wash	TRM Trim	Reflector Accessory
			FRS Frosted ⁴
		Texture	
		RWHS White RGYS Gray RBLS Black RCOS Copper RAMW Anti-Microbial White Other RX Custom Finish	

Notes:

- 1 Stem length varies by canopy configuration. See Dimensions section for details
- 2 Cable/Cord can be cut in the field to custom length
- 3 For DL only
- 4 Available only when "LW" function selected