

# NOC-2.5R

NONI 2.5" ROUND CYLINDER FAMILY

## ORDERING GUIDE

Examples: NOC-2.5RDL-CHNCSCMBL-SO35930K-DM1NUGT

CATALOG #

### HOUSING

NOC-2.5R		CHN			Optic Type	
Series/Category/Size/Shape	Function	Housing	Canopy	Mounting		Optic Type
NOC-2.5R Noni Cylinder Family 2.5" Round	DL Downlight	CHN Cylinder Housing	CS Canopy - Standard	CMBL Cable/Cord 6ft Black Cord <sup>2</sup>	CMWH Cable/Cord 6ft White Cord <sup>2</sup>	Ultra-Smooth Optic
	LW Lensed Wall Wash		CC Canopy - Conduit			CM15BL Cable/Cord 15ft Black Cord
			CX Canopy - Controls Standard	CM15WH Cable/Cord 15ft White Cord		SO30 30°
			CY Canopy - Controls Conduit	PR Stem - Rigid (Standard) Nominal 18" length from cylinder top to ceiling <sup>1</sup>		SO35 35°
				PR_ Stem - Rigid (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" <sup>1</sup>		SO40 40°
				P Stem - Swivel (Standard) Nominal 18" length from cylinder top to ceiling <sup>1</sup>		SO45 45°
				P_ Stem - Swivel (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" <sup>1</sup>		High-CBCP Optic
				SU Surface		HO20 20°
						HO25 25°
						HO30 30°
						HO35 35°
						Wall Wash Optic
						LWLW Lensed Wall Wash <sup>3</sup>

CRI/CCT	Driver Options	Control Options	U Voltage	Cylinder Housing Color
927K 90 CRI, 2700K	DM1 0-10V, ELV, TRIAC 1%	N None	U Universal Voltage 120-277V	Texture
930K 90 CRI, 3000K	ERP 0-10V, ELV, TRIAC Dim-to-Dark			WH White
935K 90 CRI, 3500K	PEQ0E Lutron Hi-Lume Premier 0.1%			GY Gray
940K 90 CRI, 4000K				BL Black
830K 80 CRI, 3000K				GT Graphite
835K 80 CRI, 3500K				PP Pink Panache
				GH Grasshopper
				Smooth
				WHS White
				GYS Gray
				BLS Black
				COS Copper
				AMW Anti-Microbial White
				Other
				X Custom Finish

### TRIM

NOC-2.5R	TRM	Reflector Insert Color	Lens
Series/Category/Size/Shape	Housing	Texture	CLR Clear
NOC-2.5R Noni Cylinder Family 2.5" Round	DL Downlight	RWH White	FRS Frosted <sup>3</sup>
	LW Lensed Wall Wash	RGY Gray	HEX Hex Cell Louver
		RBL Black	LIN Linear Spread
		RGT Graphite	NON No Lens
		RPP Pink Panache	SOL Solite
		RGH Grasshopper	
		Smooth	
		RWHS White	
		RGYS Gray	
		RBLS Black	
		RCOS Copper	
		RAMW Anti-Microbial White	
		Other	
		RX Custom Finish	

- Notes:
- 1 Stem length varies by canopy configuration. See Dimensions section for details
  - 2 Cable/Cord can be cut in the field to custom length
  - 3 Available only when "LW" function selected