

NOC-3.5R

NONI 3.5" ROUND CYLINDER FAMILY

ORDERING GUIDE

Examples: NOC-3.5RDL-CHNCSCMBL-SO35930K-DM1NUGT / NOC-3.5RDL-TRM-RPPCLR

CATALOG #

HOUSING

NOC-3.5R		CHN					Optic Type	
Series/Category/Size/Shape	Function	Housing	Canopy	Mounting				
NOC-3.5R Noni Cylinder Family 3.5" Round	DL Downlight	CHN Cylinder Housing	CS Canopy - Standard CC Canopy - Conduit	CMBL Cable/Cord 6ft Black Cord ²	CMWH Cable/Cord 6ft White Cord ²	CM15BL Cable/Cord 15ft Black Cord	CM15WH Cable/Cord 15ft White Cord	Ultra-Smooth Optic
	LW Lensed Wall Wash							SO25 25°
				PR Stem - Rigid (Standard) Nominal 18" length from cylinder top to ceiling ¹				SO30 30°
				PR_ Stem - Rigid (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" ¹				SO35 35°
				P Stem - Swivel (Standard) Nominal 18" length from cylinder top to ceiling ¹				SO40 40°
				P_ Stem - Swivel (Custom) Specify length from cylinder top to ceiling in 1 inch increments from 15" to 60" ¹				SO45 45°
				SU Surface				SO60 60°
								SO70 70°
								High-CBCP Optic
								HO20 20°
								HO25 25°
								HO30 30°
								Wall Wash Optic
								LWLW Lensed Wall Wash ³

CRI/CCT	Driver Options	Control Options	U Voltage	Cylinder Housing Color
927K 90 CRI, 2700K	DM1 0-10V, ELV, TRIAC 1% ERP 0-10V, ELV, TRIAC Dim-to-Dark	N None	U Universal Voltage 120-277V	Texture
930K 90 CRI, 3000K				WH White
935K 90 CRI, 3500K	PEQOE Lutron Hi-Lume Premier 0.1%			GY Gray
940K 90 CRI, 4000K				BL Black
830K 80 CRI, 3000K				GT Graphite
835K 80 CRI, 3500K				PP Pink Panache
				GH Grasshopper
				Smooth
				WHS White
				GYS Gray
				BLS Black
				COS Copper
				AMW Anti-Microbial White
				Other
				X Custom Finish

TRIM

NOC-3.5R		TRM			
Series/Category/Size/Shape	Function	Housing	Reflector Insert Color	Lens	
NOC-3.5R Noni Cylinder Family 3.5" Round	DL Downlight	TRM Trim	Texture	CLR Clear	
	LW Lensed Wall Wash		RWH White	FRS Frosted ⁴	
			RGY Gray	HEX Hex Cell Louver	
			RBL Black	LIN Linear Spread	
			RGT Graphite	NON No Lens	
			RPP Pink Panache	SOL Solite	
			RGH Grasshopper		
			Smooth		
			RWHS White		
			RGYS Gray		
			RBLS Black		
			RCOS Copper		
			RAMW Anti-Microbial White		
			Other		
			RX Custom Finish		

- Notes:
- 1 Stem length varies by canopy configuration. See Dimensions section for details
 - 2 Cable/Cord can be cut in the field to custom length
 - 3 Available only when "LW" function selected
 - 4 FRS is the only option for LW