

NOR-1.5S

NONI 1.5" SQUARE RECESSED FAMILY

ORDERING GUIDE

Examples: NOR-1.5SDL-RHI-SO50930K-DM1NUFWHSFRS/NOR-1.5SDL-RPP

CATALOG #

HOUSING

NOR-1.5S		RHI	Optic Type	CRI/CCT	DM1
Series/Category/Size/Shape	Function	Housing			Driver Options
NOR-1.5S Noni Recessed Family 1.5" Square	DL Downlight	RHI Remodeler Housing, IC	SO50 50°	927K 90 CRI, 2700K	DM1 0-10V, ELV, TRIAC 1%
	LW Lensed Wall Wash		LWLW Wall Wash Optic ¹	930K 90 CRI, 3000K	
				935K 90 CRI, 3500K	
				940K 90 CRI, 4000K	
				830K 80 CRI, 3000K	
			835K 80 CRI, 3500K		

Control Options	U Voltage	Reflector Flange Color	FRS Reflector Lens	Accessories
N None	U Universal Voltage 120-277V	FWHS White FGYS Gray FBLS Black FAMW Anti-Microbial White FX Custom Finish FT Flangeless FCOS Copper	FRS Frosted ²	MP1.5RMB Mounting Pan

TRIM

NOR-1.5S		TRM	Reflector Insert Color	Reflector Accessory
Series/Category/Size/Shape	Function	Housing		
NOR-1.5S Noni Recessed Family 1.5" Square	DL Downlight	TRM Trim	Texture	FRS Frosted ³
	LW Lensed Wall Wash		RWH White RGY Gray RBL Black RGT Graphite RPP Pink Panache RGH Grasshopper	
			Smooth	
			RWHS White RGYS Gray RBLS Black RCOS Copper RAMW Anti-Microbial White	
			Other	
			RX Custom Finish	

Notes:

- 1 Available only when "LW" function selected
- 2 Applies to DL only
- 3 Applies to LW only