

NOR-3.5R

NONI 3.5" ROUND RECESSED FAMILY

ORDERING GUIDE

Examples: NOR-3.5RDL-NHN-SO930K-DM1NU / NOR-3.5RDS-TRM-FWHSRPPNON / NOR-3.5RDL-SO30

CATALOG #

HOUSING

NOR-3.5R					
Series/Category/Size/Shape	Function	Housing	Optic Type	CRI/CCT	Driver Options
NOR-3.5R Noni Recessed Family 3.5" Round	DL Downlight	NHN New Construction Housing, Non-IC	HO High-CBCP Optic	927K 90 CRI, 2700K	DM1 0-10V, ELV, TRIAC 1% ²
	LWD Lensed Wall Wash, Deep		LW Wall Wash Optic ¹	930K 90 CRI, 3000K	
	LWS Lensed Wall Wash, Shallow	NHI New Construction Housing, IC	SO Ultra-Smooth Optic	935K 90 CRI, 3500K	ERP 0-10V, ELV, TRIAC Dim-to-Dark ²
	AA Adjustable Accent			940K 90 CRI, 4000K	
		CP Chicago Plenum		830K 80 CRI, 3000K	PEQOE Lutron Hi-Lume Premier 0.1%
				835K 80 CRI, 3500K	

Control Options		U Voltage	Accessories
N None		U Universal Voltage 120-277V	RMB Residential Mounting Bars
LV Lutron Vive 0-10V, 120-277V			
LVE Lutron Vive EcoSystem ⁴			

TRIM

NOR-3.5R		TRM			
Series/Category/Size/Shape	Function	Housing	Reflector Flange Color	Reflector Insert Color	Reflector Lens
NOR-3.5R Noni Recessed Family 3.5" Round	DS Downlight, Shallow (5/8" - 1 1/4" ceiling)	TRM Trim	FWHS White	Texture	CLR Clear ⁵
			FGYS Gray		RWH White
	FBLS Black		RGY Gray	HEX Hex Cell Louver	
	FAMW Anti-Microbial White		RBL Black	LIN Linear Spread ^{5,7}	
	FX Custom Finish		RGT Graphite	NON No Lens ⁵	
	FT Flangeless		RPP Pink Panache	SOL Solite ⁵	
	FCOS Copper		RGH Grasshopper		
	Smooth				
	RWHS White				
	RGYS Gray				
	RBLS Black				
	RCOS Copper				
	RAMW Anti-Microbial White				
	Other				
	RX Custom Finish				

OPTIC

NOR-3.5R		
Series/Category/Size/Shape	Function	Optic/Beam
NOR-3.5R Noni Recessed Family 3.5" Round	DL Downlight	Ultra-Smooth Optic
	LWD Lensed Wall Wash, Deep	SO25 25°
	LWS Lensed Wall Wash, Shallow	SO30 30°
	AA Adjustable Accent	SO35 35°
		SO40 40°
		SO45 45°
		SO60 60°
		SO70 70°
		High-CBCP Optic
		HO20 20°
		HO25 25°
		HO30 30°
		Wall Wash Optic
		LWLW Lensed Wall Wash ¹

- Notes:
- Available only when "LW" function selected
 - Not available with LVE control
 - Available with LVE only
 - 120V only
 - Not available with LW function
 - Available with all functions, must be selected with LW
 - Available with DS only