



L020245G

by Wiegmann
Catalog ID: L020245G

N1 45 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 2.5X2.5 Carbon Steel - Galvanized

- Galvanized 45 degrees elbow fitting.

Product Details

General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	45 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852789

Dimensions

Actual Depth	6.250 in
Actual Height	4.440 in
Actual Length	6.250 in
Actual Width	4.440 in
Depth	6 in
Height	4 in
Weight	1 lb
Width	4 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes