



## L020290G

by Wiegmann  
Catalog ID: L020290G

N1 90 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 2.5X2.5 Carbon Steel - Galvanized

- Galvanized 90 degrees elbow fitting.

## Product Details

---

### General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	90 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852727

### Dimensions

Actual Depth	6.250 in
Actual Height	4.440 in
Actual Length	6.250 in
Actual Width	4.440 in

Depth	6 in
Height	4 in
Weight	2 lb
Width	4 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	1
UL Listed	Yes