



L040490G

by Wiegmann
Catalog ID: L040490G

N1 90 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 4X4 Carbon Steel - Galvanized

- Galvanized 90 degrees elbow fitting.

Product Details

General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	90 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852734

Dimensions

Actual Depth	7.125 in
Actual Height	7.500 in
Actual Length	7.125 in
Actual Width	4.250 in
Depth	7 in
Height	8 in
Weight	3 lb
Width	4 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes