



# L1D2-800

by CMC  
Catalog ID: L1D2-800

Dual Rated Solderless Connector, wire range 800 AWG -300 AWG. TYPE:L1M2 / L1D2.CMC® L-shaped single hole solderless connectors are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. Assembly can be made with only a screwdriver or allen wrench and the connectors are reusable. 90° C Rated (486B Listed). UL listed and CSA certified.

## Product Details

### General

Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	192663088485

### Dimensions

Height	1.88 in
Length	1.88 in
Width	6.18 in

### Conductor Related

Conductor - Copper Str Size Range	800 Kcmil-300 AWG
-----------------------------------	-------------------