


L4D8-1000I

by CMC

Catalog ID: L4D8-1000I



Heavy-duty transformer connectors, uni-joint, Dual rated connectors for Aluminum or Copper conductors

- Clear Plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with aluminum radial tipped set-screws
- All mounting holes 1.75" on center line
- Designed for installation on standard two and four-hole spades
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- For installation, CMC® recommends the use of a 9" insulated Allen wrench
- A torque wrnch should be used to ensure the proper torque is achieved

Product Details

General

Cover Type	LDC-3
Number of Holes	8
Type	L-D
UPC	192663072125

Dimensions

Dimension - Hole Size inch	.56 in
Dimensions	6.19 in x 6.5 in x 1.88 in
Height	1.88 in
Length	6.19 in
Width	6.5 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	1000 Kcmil-350 Kcmil
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

