




## COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

### Threaded Conduit Fittings: LB Body Only 1-1/4" Rigid LB Type Body

C13.1



Catalog #: LB125

#### APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.  
N/A

#### PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

#### CULUS

Listed

#### NEMA

NEMA 3R Rated

#### NEC

2014 NEC Compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 1-1/4"  
Description Table: 1-1/4" Rigid LB Type Body

#### PACKAGING

Package Type: Carton  
 Std. Pkg.: 2  
 Ship Carton Qty.: 10  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 96  
 Ship Carton Length (in.): 21.65  
 Ship Carton Width (in.): 7.09  
 Ship Carton Height (in.): 9.65  
 Ctn Weight (Lbs.): 12.13  
 Pallet Qty: 480  
 UPC Number: 050169816738  
 I2of5: 50050169816733