



* Representative image

Connector, Parallel Groove

by ANDERSON
Catalog ID: LC406

Three Center Bolt Bronze Parallel Groove Connector

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Three Center Bolts
UPC	096359319580

Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Height	3.375 in
Length	5.125 in
Weight	4.606 lb
Width	3.500 in

Conductor Related

Conductor Diameter (Main) - Maximum	1.152 in
Conductor Diameter (Main) - Minimum	0.813 in
Conductor Diameter (Main) Range	0.813 - 1.152
Conductor Diameter (Tap) - Maximum	1.152 in

Conductor Diameter (Tap) - Minimum	0.811 in
Conductor Type	Copper

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com