



\* Representative image

## Connector, Parallel Groove

by FARGO  
Catalog ID: LC822XB

Single Center Bolt Aluminum Parallel Groove Connector with Bonded Copper Liner

### Product Details

#### General

Bolt Head Type	Carriage Bolt
Bolt Installation Torque (Recommended)	480 in-lbs
Cover Available	No
Inhibitor Loaded	Yes
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Body Halves	Aluminum Alloy
Material - Bolt	Galvanized Steel
Material - Bottom Member	Aluminum Alloy
Material - Casting	Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Hex Nut	Galvanized Steel
Material - Keeper	Aluminum Alloy
Material - Spacer	Aluminum Alloy
Material - Tap Liner	Bonded Copper
Material - Washer	Galvanized Steel
Plating	No
Product Category	Mechanical Connectors
Style	Single Center Bolt
Type	Parallel Groove
UPC	096359320043

#### Dimensions

Bolt Diameter	0.500 in
---------------	----------

Diameter - Bolt	0.5 in
Height	2.500 in
Length	2.250 in
Width	2.218 in

#### Conductor Related

Conductor Diameter (Main) - Maximum	0.741 in
Conductor Diameter (Main) - Minimum	0.328 in
Conductor Diameter (Main) Range	0.328 - 0.741
Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Type	Aluminum/Copper

#### Certifications and Compliance

UL Listed	No
-----------	----

**For further technical assistance, please contact us**

#### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)