

# Connector, Parallel Groove

by ANDERSON  
Catalog ID: LCC111XB

Two U-Bolt Aluminum Parallel Groove Connector



\* Representative image

## Product Details

### General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Body Halves	Aluminum Alloy
Material - Bolt	Galvanized Steel
Material - Bottom Member	Copper Alloy
Material - Casting	Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Spacer	Aluminum Alloy, Copper Lined
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359320098

### Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Weight	0.882 lb

### Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (Tap) - Maximum	0.447 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.447 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.447

## Certifications and Compliance

UL Listed	No
-----------	----

### For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)