



\* Representative image

## Chain Link

by ANDERSON  
Catalog ID: LK150

Chain Link, Forged Steel, 1.750 x 5.500" Opening x 1.375" Thick, UTS 150,000 lb

## Product Details

### General

Material	Steel
Number of Bolt Holes	0
Series	LK Series
Strength Rating - Ultimate	150000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359320494

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	5.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	3.263 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)