



Oh No!
IMAGE COMING SOON

Formed Wire Double Side Tie, C & F Neck Insulator

by FARGO
Catalog ID: LLDU4162AS

C & F Neck Insulator Double Side Tie for 556.5 and 636 ACSR- 636 and 700 AAC

- For securing the conductor in the side groove of insulators on line angles between (0°) zero degrees and (80°) eighty degrees with no more than a (40°) forty degree angle at each insulator.
- C-Neck (2-1/4" neck diameter) & F-Neck (2-7/8" neck diameter) interchangeable headstyle insulators
- Recommended for use with ANSI Class 55-2 Pin, 55-3 Pin, 55-4 Pin, 55-5 Pin, 57-1 Post, 57-2 Post, & 57-3 Post Insulators.

Product Details

General

Application	Double Side Tie
Color Code	Black-Yellow / Blue
Insulator Throat Neck Type	C & F Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452744

Dimensions

Length	22.0 in
Weight	.840 lb

Conductor Related

Conductor Diameter - Maximum	0.968 in
Conductor Diameter - Minimum	0.859 in
Conductor Diameter Range	0.859 - 0.968
Conductor Type	ACSR, AAC, AAAC, ACAR, Compacted ACSR and AWAC®

Logistics

Pallet Quantity	600 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com