

LP4-250C

by CMC
Catalog ID: LP4-250C



Insulated phase line connectors, In span phase connectors, Dual-rated connectors for aluminum or copper conductors, Cover is also included

- Designed for use on open wire or multiple cable secondaries to permit readily accessible service connections.
- The connector is constructed of high quality 6061-T6 for strength and conductivity.
- Takes up to four taps. Taps may be added later without interrupting service or removing cover.
- Impact resistant cover and clamp are clearly marked with easy-to-read cable ranges.
- Extended insulating shields on the cover make cable stripping much easier

Product Details

General

Material	Aluminum
UPC	192663082216

Dimensions

Height	2 in
Length	2.37 in
Width	0.93 in

Conductor Related

Conductor - ACSR Str Tap Range	1/0 ACSR
Conductor - AL Str Run Range	250 Kcmil-#2 AWG
Conductor - AL Str Tap Range	4/0 AWG-#14 AWG
Conductor - Copper Str Run Range	250 Kcmil-#2 AWG
Conductor - Copper Str Tap Range	4/0 AWG-#14 AWG



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

