

LP4-250

by CMC
Catalog ID: LP4-250



Insulated phase line connectors, In span phase connectors, Dual-rated connectors for aluminum or copper conductors

- Designed for use on open wire or multiple cable secondaries to permit readily accessible service connections.
- The connector is constructed of high quality 6061-T6 for strength and conductivity.
- Takes up to four taps. Taps may be added later without interrupting service or removing cover.
- Impact resistant cover and clamp are clearly marked with easy-to-read cable ranges.
- Extended insulating shields on the cover make cable stripping much easier

Product Details

General

| | |
|----------|--------------|
| Material | Aluminum |
| UPC | 192663082209 |

Dimensions

| | |
|--------|---------|
| Height | 2 in |
| Length | 2.37 in |
| Width | 0.93 in |

Conductor Related

| | |
|----------------------------------|------------------|
| Conductor - ACSR Str Tap Range | 1/0 ACSR |
| Conductor - AL Str Run Range | 250 Kcmil-#2 AWG |
| Conductor - AL Str Tap Range | 4/0 AWG-#14 AWG |
| Conductor - Copper Str Run Range | 250 Kcmil-#2 AWG |
| Conductor - Copper Str Tap Range | 4/0 AWG-#14 AWG |



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

