

LPTE30-1000G

by CMC

Catalog ID: LPTE30-1000G



Pad mounted termination enclosures, Three-Phase, NEMA 3R (rain-proof), 600 Volt Rated, Includes Grounding Straps

- Aluminum mechanical bar connector eliminates compression tools, lugs and bolt assemblies
- Aluminum enclosure is lightweight, low maintenance and has excellent corrosion resistance
- Ample working space, allowing for easier termination with a removable swinging door
- All-welded construction: welds and seams are ground smooth
- Manufactured to meet or exceed ANSI C57-12.28 for wall-mount equipment enclosure integrity
- Removable swinging doors - Doors have stainless steel lift off hinges with stainless steel three-point locking handles and recessed stainless steel penta-head bolts for security
- Finish is Munsell green, oven cured powder coat
- All mounting hardware is 18-8 stainless steel
- Any pad mount enclosure can be made with a lift-off (removable) top. In order to designate this use "LPLE" instead of "LPTE"

Product Details

General

| | |
|----------|--------------|
| Material | Aluminum |
| UPC | 192663110803 |

Dimensions

| | |
|--------|-------|
| Depth | 52 in |
| Height | 44 in |
| Width | 54 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

| | |
|----------------------|---------------------|
| Conductor Range | 1000 Kcmil-#1/0 AWG |
| Number Of Conductors | 30 |



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

