




## COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

### Threaded Conduit Fittings: LR Body Only 1-1/2" Rigid LR Type Body

C13.1



Catalog #: LR150

#### APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.  
N/A

#### PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

#### CULUS

Listed

#### NEMA

NEMA 3R Rated

#### NEC

2014 NEC Compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 1-1/2"  
Description Table: 1-1/2" Rigid LR Type Body

#### PACKAGING

Package Type:	Carton
Std. Pkg.:	2
Ship Carton Qty.:	10
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	89
Ship Carton Length (in.):	21.65
Ship Carton Width (in.):	7.09
Ship Carton Height (in.):	9.65
Ctn Weight (Lbs.):	11.69
Pallet Qty:	480
UPC Number:	050169816943
I2of5:	50050169816948