




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: LR Body Only 3" Rigid LR Type Body

C13.1



Catalog #: LR300

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3"
Description Table: 3" Rigid LR Type Body

PACKAGING

Package Type: Carton
 Std. Pkg.: -
 Ship Carton Qty.: 1
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 312
 Ship Carton Length (in.): 13.98
 Ship Carton Width (in.): 5.59
 Ship Carton Height (in.): 6.69
 Ctn Weight (Lbs.): 3.75
 Pallet Qty: 120
 UPC Number: 050169816974
 I2of5: 50050169816979