



Oh No!
IMAGE COMING SOON

Formed Wire Spool Tie

by FARGO
Catalog ID: LRO4022AS

Spool Tie for 3/0 ACSR, 3/0 AAC, 3/0 AAAC- #4, #1 and 1/0 Plastic Jacketed

- For securing the conductor in the side groove of horizontally or vertically mounted spool insulators.
- For 1-3/4" neck diameter interchangeable headstyle insulators
- Recommended for use with ANSI Class 53-1, 53-2 & 53-3 Spool Insulators.

Product Details

General

Application	Spool Tie
Color Code	Orange
Insulator Throat Neck Type	Spool
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359467847

Dimensions

Length	31 in
Weight	.320 lb

Conductor Related

Conductor Diameter - Maximum	0.520 in
Conductor Diameter - Minimum	0.460 in
Conductor Diameter Range	0.460 - 0.520
Conductor Type	ACSR, AAC, AAAC, ACAR, Compacted ACSR and AWAC*

Logistics

Pallet Quantity	2000 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com