



12 A, Type T (ANSI) Fuselinks, 26" Length, Removable Head

by CHANCE Utility
Catalog ID: M12TA

12 amp, Type T (ANSI) Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.



Product Details

General

Fuse Head Style	Removable
Fuselink Type	Type T (ANSI)
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359043157

Dimensions

Length - Fuselink	26" (660.4mm)
Weight	0.059 lb

Electrical Ratings

Amperage Rating	12 A
-----------------	------

Logistics

Pallet Quantity	4800 EA
Standard Package	10

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com