



140 A, Type T (ANSI) Fuselinks, 23" Length, Solid Head

by CHANCE Utility
Catalog ID: M140T23

140 amp, Type T (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



Product Details

General

| | |
|----------------------------|---|
| Fuse Head Style | Solid |
| Fuselink Type | Type T (ANSI) |
| Required Cutout Fuseholder | 200 Amp (Do not use in a 100 amp fuseholder.) |
| Type | Fuselinks |
| UPC | 096359043393 |

Dimensions

| | |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
| Weight | 0.245 lb |

Electrical Ratings

| | |
|-----------------|-------|
| Amperage Rating | 140 A |
|-----------------|-------|

Logistics

| | |
|------------------|---------|
| Pallet Quantity | 2400 EA |
| Standard Package | 5 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com