



## 140 A, Type T (ANSI) Fuselinks, 26" Length, Removable Head

by CHANCE Utility  
Catalog ID: M140TA

140 amp, Type T (ANSI) Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.



## Product Details

### General

Fuse Head Style	Removable
Fuselink Type	Type T (ANSI)
Required Cutout Fuseholder	200 Amp (Do not use in a 100 amp fuseholder.)
Type	Fuselinks
UPC	096359043379

### Dimensions

Length - Fuselink	26" (660.4mm)
Weight	0.451 lb

### Electrical Ratings

Amperage Rating	140 A
-----------------	-------

### Logistics

Pallet Quantity	2400 EA
Standard Package	5

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)