



# 15 A, Type T (ANSI) Fuselinks, 26" Length, Removable Head

by CHANCE Utility  
Catalog ID: M15TA

15 amp, Type T (ANSI) Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.



## Product Details

### General

Fuse Head Style	Removable
Fuselink Type	Type T (ANSI)
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359043577

### Dimensions

Length - Fuselink	26" (660.4mm)
Weight	0.078 lb

### Electrical Ratings

Amperage Rating	15 A
-----------------	------

### Logistics

Pallet Quantity	4800 EA
Standard Package	10

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)