



* Representative image

3/4" Polypropylene Rope

by CHANCE Utility
Catalog ID: M18955

ROPE, 3/4" BLUE POLYPROPYLENE 600FT, Polypropylene Rope was selected for its strength, light weight and resistance to moisture. Water accumulation on the surface can be readily removed by shaking vigorously and wiping with an absorbent cloth. As with any hot line rope, polypropylene should be stored in a dry place. Three strand construction is orange with black and green tracer. NOTE: While Polypropylene Rope has excellent dielectric strength, water accumulation between strands is a definite hazard. Also, Polypropylene Rope should not be used in running hitches or any place friction heating can occur. Not for use on capstans.

Product Details

General

Material	Polypropylene
Max Load Lbs.	1090 lb
Tensile Strength	7,650 lb
Type	Load Lift Assist
UPC	096359043911

Dimensions

Diameter	0.75 in
Length	7200 in
Weight	0.14 lb

Logistics

Standard Package	600
------------------	-----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com