



* Representative image

LoadLocker Ammeter, Up to 400kV, 60 Hertz Unit

by CHANCE Utility
Catalog ID: MEAMP21RW

AMMETER LOADLOOKER, UP TO 400KV (60HZ), Instead of you manipulating a hinged or clamp-type inductive pick-up, the patented LoadLocker electronically closes the loop for you. Its unique U-shape jaw senses the amperage present between its tines. The open-end design lets you check loads on components not accessible by other hot-line ammeters. Live-line-ready hotstick mount A standard fitting on the LoadLocker lets it mount on your insulated hotsticks just as any other universal tool. Your hot-line crews can begin using it immediately, in compliance with prescribed safe-working clearances for your system voltages. Simple push button operation, direct-reading accuracy, a single button controls the operation. Push it once to turn on the LoadLocker. Push it a second time and LoadLocker will display the word HOLD and continue to display the next reading it "sees" until you push the button to clear it. This lets you bring it down from the line to eye level to read it. After five idle minutes, the unit will turn itself off or you can manually turn it off by keeping the button depressed for five seconds. A detailed Operators Manual and storage case are included with each LoadLocker.

Product Details

General

Style	LoadLocker Ammeter, Up to 400kV
UPC	096359241676

Dimensions

Jaw Width	3.86"
Weight	3.1 lb

Electrical Ratings

Amperage - Display Range	0-99.9 Amperes (0.1 Amp increments); 100-1999 Amperes (1.0 Amp increments)
Amperage Rating	Up to 2000 A
Withstand Voltage	Up to 400 kV

Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com