



N12604824

by Wiegmann
Catalog ID: N12604824

N12 Two Door Floor-Mount 60X48X24 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosed equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment found in automotive, pulp and paper, wood products, textile, and similar industries.

Product Details

General

Application	Designed to protect electronic controls, components and instruments in typical industrial environments from dust, dirt, oil and dripping water. These enclosures are used to machine tool applications for housing motor starters, drives, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment found in automotive, pulp and paper, wood products, textile and similar industries.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3 Point Keylocking-Padlocking Combo
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Floor Mount
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725412556

Dimensions

Depth	24 in
Height	60 in
Weight	465 lb

Width	48 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes