



N1C101004

by Wiegmann
Catalog ID: N1C101004

N1 Hinged-Cover 10X10X4 Carbon Steel - Gray

Designed for use as control enclosures and instrument cases in areas not required oil-tight and dust-tight specifications.

- Bodies and doors fabricated from 14 gauge steel. Continuous hinged covers. Mounting holes on back of cabinet. Grounding provisions provided. Doors furnished standard with flushmount quarter-turn style latch. Weldnuts provided for mounting optional back panels.

Product Details

General

Application	Designed for use as control enclosures and instrument cases in areas not requiring oil-tight and dust-tight specifications.
Color	Gray
Construction	Seam and Spot Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725340200

Dimensions

Depth	4 in
Height	10 in
Weight	8 lb
Width	10 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 1
UL Listed	Yes