



N1C364811

by Wiegmann
Catalog ID: N1C364811

N1 Hinged-Cover 36X48X11 Carbon Steel - Gray

Designed for use in control and instrumentation applications in areas which do not require oil-tight and dust-tight specifications.

- Bodies and doors fabricated from 14 gauge steel. Continuous hinged doors. Doors are easily removable by pulling the hinged pin. Collar studs provided for mounting optional back panels. External mounting feet provided. Grounding provisions provided. Doors are furnished standard with flushmount quarter-turn latch.

Product Details

General

Application	Designed for use in control and instrumentation applications in areas which do not require oil-tight and dust-tight specifications.
Color	Gray
Construction	Seam and Spot Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Feet
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725341979

Dimensions

Actual Depth	10.94 in
Actual Width	36.000 in
Depth	11 in
Height	48 in
Weight	124 lb

Width	36 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 1
UL Listed	Yes