



N4121212061PTC

by Wiegmann
Catalog ID: N4121212061PTC

N412 Single Door Wall-Mount Ultimate 1-Point Handle 12X12X6 Carbon Steel - Gray

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less holes or knockouts. Doors are interchangeable and easily removable. Grounding studs are welded to door and body assuring a positive ground. Print pocket is provided. Doors are sealed with poured-in-place gasket. Mounting holes in rear of enclosure. Collar studs for mounting optional back panel. With 1pt Keylocking/padlocking Combo Handle.

Product Details

General

Application	Hubbell Wiegmann N412IPTC ULTIMATE Series Enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil water, or other contaminants are present. Streamlined
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Smooth
Latches Type	1-Point Handle
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Mounting Type	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725873418

Dimensions

Actual Depth	7.75 in
Actual Width	12.06 in
Cubic Capacity	864 cu.in

Depth	6 in
Height	12 in
Weight	18 lb
Width	12 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes