



N412242608CDSSA

by Wiegmann
Catalog ID: N412242608CDSSA

N412 Single Door Flanged Disconnect Ultimate Series 24X26X8 316 Stainless Steel

- Bodies and doors are fabricated from 316L stainless steel
- Seams are continuously welded and ground smooth
- Doors are sealed with a poured in place gasket
- Mounting holes are located in the back of the enclosure
- Latching system interlocks with the disconnect handle for added safety

Bodies and doors fabricated from 14 gauge 316 stainless steel. Continuously plasma welded seams. Increased tub opening for better access. Concealed hinges. Easy to remove doors are interchangeable. Grounding provisions included. Doors are sealed with poured-in-place polyurethane gasket. Mounting holes in rear of enclosure. Studs for mounting optional sub panel. Door latching system installed on door with a slotted insert defeater mechanism to open. Latching system interlocks with the disconnect handle for added safety. 3pt latch system.

Product Details

General

Application	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers, available with or without Wiegmann-supplied defeater door handle and handle hardware.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	2-Point
Listings	UL, CSA
Material	316 Stainless Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure

UPC	786725869527
-----	--------------

Dimensions

Cubic Capacity	4992 cu.in
Depth	8 in
Height	24 in
Weight	57 lb
Width	26 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes