



* Representative image

N412302008SS3PTC

by Wiegmann
Catalog ID: N412302008SS3PTC

N412 Single Door Wall-Mount Ultimate 3-Point Handle 30x20x8 Carbon Steel - Gray.

Bodies and doors are fabricated from 304 or 316L stainless steel. Seams are continuously welded and ground smooth. Increased opening for better access. Ground stud located on the door and tub. Doors are sealed with a poured in place gasket. Mounting holes are located in the back of the enclosure. 3-point 316L stainless steel padlocking handle.

Product Details

General

Application	Bodies and doors are fabricated from 304 or 316L stainless steel. Seams are continuously welded and ground smooth. Increased opening for better access. Ground stud located on the door and tub. Doors are sealed with a poured in place gasket. Mounting holes are located in the back of the enclosure. 3-point 316L stainless steel padlocking handle.
Color	Stainless Steel
Finish Type	Smooth Grained Finish
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725889679

Dimensions

Actual Depth	8 in
Actual Height	30 in
Actual Width	20 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12