



N4123630163PTC

by Wiegmann
Catalog ID: N4123630163PTC

N412 Single Door Wall-Mount Ultimate 3-Point Handle 36X30X16 Carbon Steel - Gray

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less holes or knockouts. Doors are interchangeable and easily removable. Grounding studs are welded to door and body assuring a positive ground. Print pocket is provided. Enclosures are supplied with closed cell neoprene gasket. Mounting holes in rear of enclosure. Collar studs for mounting optional back panel. With 3pt Keylocking/padlocking Combo Handle.

Product Details

General

Application	Hubbell Wiegmann N4123PTC ULTIMATE Series Enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil water, or other contaminants are present. Streamlined
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3-Point Keylocking/Padlocking
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Mounting Type	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725869312

Dimensions

Actual Depth	17.75 in
Actual Height	39 in
Cubic Capacity	17280 cu.in

Depth	16 in
Height	36 in
Weight	104 lb
Width	30 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes