

N412D426012C

by Wiegmann

Catalog ID: N412D426012C

N412 Double Door Wall-Mount Ultimate 42X60X12 Carbon Steel - Gray

The N412D_C ULTIMATE Series Two Door enclosure is designed to house and protect electrical and electronic components in harsh, dirty environments. For use in installations where dirt, dust, oil, water and other contaminants are present.

- Bodies and doors are fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Increased tub opening for easier access
- Grounding provisions are provided
- Doors are sealed with a poured in place gasket
- Studs for mounting ULTIMATE Series back panels are provided



Product Details

General

Color	Ansi-61 Gray Smooth
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3-Point Handle
Material	Carbon Steel
Mounting Type	Mounting Holes
Number of Doors (Fixed)	2
Series	Ultimate
Type	Enclosure
UPC	786725889792

Dimensions

Cubic Capacity	30240 cu.in
Depth	12 in
Height	42 in
Weight	250 lb
Width	60 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	NEMA 3R;NEMA 4;NEMA 12;NEMA 13

