

NA500-5

by CMC

Catalog ID: NA500-5

Dual-Rated For Aluminum or Copper Conductors, CO-OX oxide inhibitor is omitted

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with radial-tipped set-screws
- 105 ° C rated black plastisol cover available
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench



Product Details

General

Material	Aluminum
----------	----------

Dimensions

Height	1.41 in
Length	6.03 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
-----------------	---------------------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

