



NACC250-2A

by CMC
Catalog ID: NACC250-2A

Clear Insulated Secondary Connectors, Dual-Rated For Aluminum or Copper Conductors

- CMC® Flex tap is available in two through eight conductor configurations in five conductor sizes
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Connector is encapsulated in clear PVC rated at 240 volts per mil
- Clear cover allows visual inspection of conductors during installation
- Fully tested to ANSI C119.4 for Class 'A' connectors

Product Details

General

Material	Aluminum
UPC	192663087235

Dimensions

Height	2.13 in
Length	1.87 in
Width	2.6 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	250 Kcmil - #12 AWG
-----------------	---------------------

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - UL Recognized	Yes
RUS Listed Reference	No



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

