

NACC250-6B

by CMC

Catalog ID: NACC250-6B



Clear Insulated Secondary Connectors, Dual-Rated For Aluminum or Copper Conductors

- CMC® Flex tap is available in two through eight conductor configurations in five conductor sizes
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Connector is encapsulated in clear PVC rated at 240 volts per mil
- Clear cover allows visual inspection of conductors during installation
- Fully tested to ANSI C119.4 for Class 'A' connectors

Product Details

General

Material	Aluminum
----------	----------

Dimensions

Dimensions	5.37 in x 2.6 in x 2.13 in
Height	2.13 in
Length	5.37 in
Width	2.6 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	250 Kcmil - #12 AWG
-----------------	---------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Recognized	Yes

RUS Listed Reference

No



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

