

NACC4-5B

by CMC

Catalog ID: NACC4-5B



Dual-Rated For Aluminum or Copper Conductors

- CMC® Flex tap is available in two through eight conductor configurations in five conductor sizes
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Connector is encapsulated in clear PVC rated at 240 volts per mil
- Clear cover allows visual inspection of conductors during installation
- Fully tested to ANSI C119.4 for Class 'A' connectors

Product Details

General

| | |
|----------|----------|
| Material | Aluminum |
|----------|----------|

Dimensions

| | |
|--------|---------|
| Height | 1.12 in |
| Length | 3 in |
| Width | 1.5 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

| | |
|-----------------|-------------------|
| Conductor Range | #4 AWG to #14 AWG |
|-----------------|-------------------|

Certifications and Compliance

| | |
|-------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - UL Recognized | Yes |
| RUS Listed Reference | No |



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

