

NACC750-8B

by CMC

Catalog ID: NACC750-8B

Clear Insulated Secondary Connectors, Dual-Rated for Aluminum or Copper Conductors

Door switch with plain plunger and release button for use with LED strip light.



Product Details

General

Application	Lighting
Rated Current	28 - 0.27 A
Type	NACC Door Switch
UPC	786725885701

Dimensions

Actual Depth	1.16 in
Actual Height	3.5 in
Actual Width	1.18 in
Depth	1 in
Dimensions	10.5 in x 3 in x 2.75 in
Height	2.75 in
Length	10.5 in
Width	3 in

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	600 V

Conductor Related

Conductor Range	750 Kcmil - #2 AWG
Number Of Conductors	8



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: jrex@cmclugs.com

