



## NP2424PP

by Wiegmann  
Catalog ID: NP2424PP

Perforated Panel (N1/3R/4/12) 21X21 Carbon Steel - White

The NP Series perforated back panels are used in large, wall-mount enclosures including the N1, RHC, N4, N4X, and N412, allowing the user to mount many types of electrical components.

- Fabricated from carbon steel
- Painted with white polyester powder
- Perforated panels accept self-tapping screws which eliminates the need to measure, mark, and drill when mounting components

Perforated panels are fabricated from 14 gauge. Panel with any side over 20.00" has 3/4" flange on all sides. Panels fit the following enclosures: NEMA 1, Large (NIC); NEMA 3R, hinged Cover (RHC, Large); NEMA 4, 412, & 4X Single Door (N12, N4, N412, SSN4, SSN43PT, SSN43PTW); NEMA 12, 2-Door Wall-Mount (WAWF), Single Door; Right Flange Disconnect (SDN12, ABM12); Large JIC (B-CH, Large) Single door N12.

## Product Details

### General

Application	For use with NEMA 1, 3R, 12, 4, and 4X wall-mounts.
Color	White
Construction	Flanged
Finish Type	Smooth hybrid paint
Material	Carbon Steel
Mounting Method	Mounting Holes
Series	NP
Type	Back Panel
UPC	786725866281

### Dimensions

Actual Height	1.375 in
Actual Width	19.25 in
Height	1 in
Weight	6 lb
Width	19 in