

NPB4-4/01

by CMC
Catalog ID: NPB4-4/01



Transformer eyebolt connectors, blind hole wire port, dual-rated connectors for aluminum or copper conductors

- For moisture resistance, conductor ports are not drilled through the body.
- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- For installation on equipment secondary adaptors.
- Stud is electro-tin plated.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.

Product Details

General

Material	Aluminum Alloy, 6061-T6
Type	Adapters
UPC	192663074143

Dimensions

Diameter - Stud	0.5 in
Height	1.87 in
Length	4 in
Stud Inside Diameter	0.5 in
Width	1.35 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	#4/0 AWG to #14 AWG
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

