

NSSM250-4SLI

by CMC

Catalog ID: NSSM250-4SLI



Stud-mount transformer connectors, Dual rated connectors for Aluminum or Copper conductors, NSSM with patented Keyhole mounting, Street light tap available

- NSSM with patented Keyhole mounting.
- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Offers fast, economical, reusable, dependable connections for right or left-hand installations.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- 105°C Rated black plastisol cover available.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

| | |
|----------|-------------------------|
| Material | Aluminum Alloy, 6061-T6 |
| UPC | 192663070879 |

Dimensions

| | |
|--------|---------|
| Height | 1.13 in |
| Length | 5.56 in |
| Width | 0.88 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

| | |
|----------------------|---------------------|
| Conductor Range | 250 Kcmil - #12 AWG |
| Number Of Conductors | 4 |



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

