


NUB500-4SL

by CMC
 Catalog ID: NUB500-4SL



Stud-mount transformer connectors, slip-fit with patented sharkbite™ mount, CO-OX Oxide inhibitor is omitted, Street light tap available

- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Supplied with aluminum radial-tipped set screws.
- Includes inhibitor in all ports and stud-mounting hole.
- Patented two-in-one Sharkbite™ mounting hole feature allows the connector to fit on a 5/8" - 11 or 1" - 14 transformer stud. Both sizes fit in the same hole.
- Sharkbite™ mounting hole feature provides 10 times the surface area contact on the stud over traditional connectors.
- The Sharkbite™ feature also securely locks the connector onto the stud to eliminate wobble when installing the conductors.
- Fully tested to ANSI C119.4 for Class 'A' connectors.

Product Details

General

Material	Aluminum Alloy, 6061-T6
----------	-------------------------

Dimensions

Height	1.75 in
Length	6.83 in
Width	1.38 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

