




Tee, Aluminum Compression

by FARGO
Catalog ID: ORT221515

Tee, Aluminum Compression, Open run Cable to Cable, 1.331-1.425 Main to 1.331-1.425 Tap. TEE, AL COMP 1.33-1.42 IN - 1.33-1.42 IN



* Representative image

Product Details

General

Material	Aluminum
Number of Ground Braid Lug Holes	0
Type	Tee, Aluminum Compression
UPC	096359451976

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Run Length before Compression	20.1 in
Tap Length before Compression	7.2 in
Weight	5.200 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter (Main) - Maximum	1.33 in
Conductor Diameter (Main) - Minimum	1.236 in
Conductor Diameter (Main) Range	1.236 - 1.33

Conductor Diameter (Tap) - Maximum	1.33 in
Conductor Diameter (Tap) - Minimum	1.236 in
Conductor Diameter (Tap) Range	1.236 - 1.33
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Logistics

Carton Quantity	3 EA
Pallet Quantity	60 EA

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com