



by Wiegmann
Catalog ID: PB4SBC

N4 Blank 4 Square Pushbutton Cover Only 7.2X6.2X3 Carbon Steel - Gray

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Enclosures have internal detachable hinges to hold cover open during wiring, yet permit quick removal. Grounding provisions provided.

Product Details

General

Application	Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Number of Holes	0
Series	PB
Type	Standard Pushbutton Enclosure
UPC	786725845545

Dimensions

Actual Depth	7.25 in
Actual Height	7.250 in
Actual Width	6.250 in
Depth	7 in
Height	7 in

Weight	4 lb
Width	6 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4
UL Listed	Yes