



## PBGX9

by Wiegmann  
 Catalog ID: PBGX9

N12 22.5 MM 9 Pushbutton Enclosure 8.5X6.5X4.2 Carbon Steel - Gray

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" miniature pushbutton holes accept all standard brands of miniature push buttons, switches, and pilot lights. Enclosures have internal detachable hinges to hold cover open during wiring, yet permit quick removal. Grounding provisions provided.

## Product Details

### General

Application	Designed to hold all standard brands of miniature oil-tight pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Number of Holes	9
Series	PBGX
Type	Miniature Pushbutton Enclosure
UPC	786725431939

### Dimensions

Actual Depth	4.25 in
Actual Height	8.500 in
Actual Width	6.500 in
Depth	4 in

Height	9 in
Weight	6 lb
Width	7 in

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	12
UL Listed	Yes